



Delivering test and measurement advantages for HVAC/R professionals worldwide

Test the TPI advantage

1020

APPLICATIONS

- Airborne contamination monitoring & testing
- Clean rooms
- Emissions sourcing
- Filter testing
- IAQ monitoring & testing



1020: Handheld Particle Counter

• Small Size -Big Performance

The handheld TPI 1020 is a portable particle counter that counts particles down to 0.3 microns-giving you portability and reliability at the lowest price in the industry.

• Completely Self-Contained-Selectable Particle Sizes

Don't let the size fool you-the TPI 1020 is completely self-contained with its own internal battery and sample pump, and is programmable, allowing you to choose your particle size of interest from five sizes: 0.3, 0.5, 1.0, 2.0, or 5.0 microns.

• Fast Sampling

Unlike other counters that can take up to a minute to deliver results, the TPI 1020 starts delivering volumetric concentration results in about 3 seconds! This facilitates quick multi-site sampling, tracing particle sources and site particle trending.

• Simple Operation

Only two front-panel buttons control the size channels and sample cycle. Power is controlled by the Start / Stop button.

• Battery or AC Powered

The self-contained battery pack powers the unit for 30 hours of typical intermittent operation, and for up to 12 hours of continuous use. The included AC charger / adapter operates the counter, even when the battery pack is discharged, and recharges the depleted battery in 2.5 hours.

Test Products
International, Inc.
Headquarters:
9615 SW Allen Blvd.
Beaverton, OR 97005
USA

503-502-9197
Fax: 503-520-1225
email:
info@tpi-
thevalueleader.com

[www.tpi-
thevalueleader.com](http://www.tpi-thevalueleader.com)

Specifications

Particle Size Range	>0.3, >0.5, >1.0, >2.0, and >5.0 μm (selectable)
Concentration Range	0 – 3,000,000 particles per cubic foot (105,900 particles/L)
Accuracy	$\pm 10\%$, to calibration aerosol
Sensitivity	0.3 μm
Flow Rate	0.1 cfm (2.83 lpm)
Sample Time	1 minute total (reading updated every 3 seconds)